

MTG Fastening Solutions

Thanks to our experience in the development of speed rivet technology on one-way mandrels of more than 30 years, we are able to guarantee a high degree of reliability also in case of technically demanding needs.

We produce pneumatic and hydro-pneumatic rivet setting tools for industrial purposes.


Up to 200 speed rivets on one-way mandrels - with wire lengths between 400 and 1,110 mm - can be used with our technology without any need for a change of the mandrel.

We manufacture different versions of rivet setting tools with appropriate noses and riveting systems depending on the workpiece and the place of work.

According to the respective application we provide individual and multiple riveting stations as complete work places at which several speed rivets can be inserted into a component at the same time.

The rivet modules and devices are tailored to the application profile of our customer.

Our customer service representative appreciates to visit you and to give advice on site.



MTG

Hartmut Thiele GmbH

Fastening Solutions · Speed Rivet Systems

Speed Rivet Equipment

The New Generation

DZ 1000 & DZ 1100



MTG

Hartmut Thiele GmbH

Fastening Solutions · Speed Rivet Systems

Röntgenstraße 3

D-30890 Barsinghausen

Phone +49 (0) 51 05 - 52 19 - 0

Fax +49 (0) 51 05 - 52 19 52

www.nietautomation.de

info@nietautomation.de



MORE USER-FRIENDLY, MORE EFFICIENT AND MORE INNOVATIVE

The MTG rivet setting equipment of the new generation DZ 1000 and DZ 1100 - durable and reliable!

The development of the new generation of our rivet setting equipment focused on an improved handling for a faster working.

Benefit from new additional advantages for your production:

- approx. 400g less weight compared with the older devices
- fixed barrel during setting
- the mandrel is pulled into the device during setting
- therefore no recoil
- improved ergonomics
- pleasant handling thanks to the plastic components
- and newly arranged 45° air connection
- the sliding valve of the mandrel clamping is not activated when laying the device down
- maintenance-friendly exchange of the jaws without auxiliary tools
- more comfortable surface feel
- other versions available on request

Combine the new generation with our progressive patented rotary opening nose DZM and achieve a maximum saving of time.

Our MTG team will be happy to provide advice!

